



MINIATURE FUSES WITH INDICATOR
CERAMIC TUBE

M

Size
5 x 25 mm


Rated voltage
250 V

medium time lag

Standard
DIN 41576 Part 2

Rated current	Part No.	Voltage drop mV	Color code	Rated breaking capacity	Weight (kg/100)	Pack
80 mA	172 526	520	grey	80 A	0.15	100
100 mA	172 526	500	red	80 A	0.15	100
125 mA	172 526	500	violet	80 A	0.15	100
160 mA	172 526	400	orange	80 A	0.15	100
200 mA	172 526	400	blue	80 A	0.15	100
250 mA	172 526	375	yellow	1500 A	0.15	100
315 mA	172 526	410	black	1500 A	0.15	100
400 mA	172 526	280	brown	1500 A	0.15	100
500 mA	172 526	250	white	1500 A	0.15	100
630 mA	172 526	220	green	1500 A	0.15	100
800 mA	172 526	400	grey	1500 A	0.15	100
1 A	172 526	350	red	1500 A	0.15	100
1.25 A	172 526	315	lilac	1500 A	0.15	100
1.6 A	172 526	480	orange	1500 A	0.15	100
2 A	172 526	360	blue	1500 A	0.15	100
2.5 A	172 526	300	yellow	1500 A	0.15	100
3.15 A	172 526	250	black	1500 A	0.15	100
4 A	172 526	180	brown	1500 A	0.15	100
5 A	172 526	180	white	1500 A	0.15	100
6.3 A	172 526	160	green	1500 A	0.15	100
(8) A	172 526	160	grey	1500 A	0.15	100
(10) A	172 526	160	red	1500 A	0.15	100

(...) = not standardized



Pre-arcing time limits

Rated current	1.5 I _n	2.0 I _n	2.75 I _n	4 I _n	10 I _n
80 mA	> 1 h	< 2 min.	-	40 ms	5 ms
100 mA				500 ms	30 ms
125 mA					
1.5 A	> 1 h	< 30 min.	-	60 ms	5 ms
1.6 A				2 s	70 ms
6.3 A					

